

Product information

71 32 200

KNIPEX CoBolt®

Compact Bolt Cutter



- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to Ø 5.2 mm
- Efficient joint design ensures exceptional cutting performance with
- With recess for easier cutting of thicker wires
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened







General	
Article No.	71 32 200
EAN	4003773066880
Pliers	black atramentized
Handles	with slim multi-component grips
Weight	370 g
Dimensions	200 x 62 x 24 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

technical change and errors excepted