

Product information

71 42 200

KNIPEX CoBolt®



- With slim multi-component grips without collar for better handling and easier transport
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to Ø 5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

MM  $\angle 20^\circ$

General

Article No.	71 42 200
EAN	4003773087212
Handles	with slim multi-component grips
Weight	380 g
Dimensions	200 x 62 x 24 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

technical change and errors excepted