

## **Product information**

## 72 62 200

## **High Leverage Flush Cutter**

For soft metal and plastic



 Space for hands and flush cutting due to 20° angled head with joint bar on one side

components

 Opening spring and locking device are integrated in the handles also for comfortable work and protected transport

For easy and flush cutting of soft metal or thicker profiles and plastic

- Precision cutting edges for soft material
- Durable due to induction-hardened cutting edges to 59 HRC

 Energy-saving, flush cutting also of thick workpieces thanks to extremely effective lever action mechanism with very low friction

• Chrome vanadium electric steel, forged, multi stage oil-hardened





General	
Article No.	72 62 200
EAN	4003773081913
Pliers	black atramentized
Handles	with slim multi-component grips
Weight	375 g
Dimensions	200 x 62 x 24 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 6.0 mm

technical change and errors excepted



Clean, flush cutting of copper conductor rails



Ideal for the flush cutting plastic sprues with large diameters

## **KNIPEX** Quality – Made in Germany



