

## **Product information**

## 74 02 160

## **High Leverage Diagonal Cutter**

**DIN ISO 5749** 



- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened





General	
Article No.	74 02 160
EAN	4003773023081
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	209 g
Dimensions	160 x 57 x 21 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.4 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacities piano wire (diameter)	Ø 2.0 mm

technical change and errors excepted



