

Product information

74 02 200 T

High Leverage Diagonal Cutter

DIN ISO 5749



- Pliers with tether attachment point for mounting a fall protection system
- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened





General	
Article No.	74 02 200 T
EAN	4003773080084
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	305 g
Dimensions	200 x 55 x 23 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 4.2 mm
Cutting capacities hard wire (diameter)	Ø 3.0 mm
Cutting capacities piano wire (diameter)	Ø 2.5 mm
Drop Protection System	yes

technical change and errors excepted

KNIPEX Quality – Made in Germany





