


## **Product information**

# 74 02 200

### **High Leverage Diagonal Cutter**

DIN ISO 5749



- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
  Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- · ·

You Tube

#### General

74 02 200
4003773040309
black atramentized
polished
with multi-component grips
304 g
200 x 52 x 21 mm
DIN ISO 5749
does not contain SVHC
not applicable
Ø 4.2 mm
Ø 3.0 mm
Ø 2.5 mm

technical change and errors excepted



