

Product information

76 01 125

Diagonal Cutter

For electromechanics

DIN ISO 5749


- With sharp, precisely aligned cutting edges
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- Lap joint
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	76 01 125
EAN	4003773044482
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	85 g
Dimensions	125 x 52 x 12 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 2.3 mm
Cutting capacities hard wire (diameter)	Ø 1.5 mm
Cutting capacities piano wire (diameter)	Ø 0.6 mm
Cutting capacities soft wire (diameter)	Ø 0.4 – 3 mm
Jaw length (B)	16 mm
Jaw thickness (joint) (D)	9 mm
Head width (A)	14.5 mm

Technical details



technical change and errors excepted