

## **Product information**

## 83 10 010

## Pipe Wrench 90°

DIN 5234



**∭** <u>√</u>90°

- Swedish pattern
- 90° angled jaws Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56
- Chrome vanadium electric steel, forged, multi stage oil-hardened

| General         |                       |  |
|-----------------|-----------------------|--|
| Article No.     | 83 10 010             |  |
| EAN             | 4003773014188         |  |
| Pliers          | red powder-coated     |  |
| Weight          | 779 g                 |  |
| Dimensions      | 310 x 57 x 19 mm      |  |
| Standard        | DIN 5234              |  |
| REACH compliant | does not contain SVHC |  |
| RoHS compliant  | not applicable        |  |

| Technical details               |          |
|---------------------------------|----------|
| Clamping width                  | 42 mm    |
| Capacities for pipes (diameter) | Ø 1 5/8  |
| Capacities for pipes (diameter) | Ø 42 mm  |
| Capacities for nuts             | 42 mm    |
| Inner diameter, inches          | Ø 1 Inch |

technical change and errors excepted



