

Product information

83 10 015

Pipe Wrench 90°

DIN 5234



Swedish pattern •

- •
- 90° angled jaws Jaws with offset teeth in opposite direction •
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut ٠ ٠
- Red powder-coated, jaws bright ground Gripping jaws with specially hardened teeth, hardness approx. 56 • HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened •

$\square $	<u>9</u> 0°
------------	-------------

General

Article No.	83 10 015	
EAN	4003773014195	
Pliers	red powder-coated	
Weight	1,415 g	
Dimensions	420 x 67 x 24 mm	
Standard	DIN 5234	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	
Technical details		
Clamping width	60 mm	
Capacities for pipes (diameter)	Ø 2 3/8 Inch	
Capacities for pipes (diameter)	Ø 60 mm	
Capacities for nuts	60 mm	
Inner diameter, inches	Ø 1 1/2 Inch	

technical change and errors excepted



