

Product information

83 10 020

Pipe Wrench 90°

DIN 5234



Swedish pattern • •

- 90° angled jaws Jaws with offset teeth in opposite direction • • Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut ٠
- ٠
- Red powder-coated, jaws bright ground Gripping jaws with specially hardened teeth, hardness approx. 56 • HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened •

General

Article No.	83 10 020
EAN	4003773014201
Pliers	red powder-coated
Weight	2,600 g
Dimensions	560 x 82 x 30 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Clamping width	70 mm
Capacities for pipes (diameter)	Ø 2 3/4
Capacities for pipes (diameter)	Ø 70 mm
Capacities for nuts	70 mm
Inner diameter, inches	Ø 2 Inch

technical change and errors excepted



