

Product information

83 10 040

Pipe Wrench 90°

DIN 5234



- Swedish pattern
- 90° angled jaws Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56
- Chrome vanadium electric steel, forged, multi stage oil-hardened

| General | |
|-----------------|-----------------------|
| Article No. | 83 10 040 |
| EAN | 4003773022336 |
| Pliers | red powder-coated |
| Weight | 4,921 g |
| Dimensions | 750 x 88 x 25 mm |
| Standard | DIN 5234 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

| Technical details | | |
|---------------------------------|----------|--|
| Clamping width | 130 mm | |
| Capacities for pipes (diameter) | Ø 5 1/8 | |
| Capacities for pipes (diameter) | Ø 130 mm | |
| Capacities for nuts | 130 mm | |
| Inner diameter, inches | Ø 4 Inch | |

technical change and errors excepted



