

Product information

83 20 015

Pipe Wrench 45°

DIN 5234



- · Swedish pattern
- 45° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General		
Article No.	83 20 015	
EAN	4003773014225	
Pliers	red powder-coated	
Weight	1,408 g	
Dimensions	430 x 59 x 24 mm	
Standard	DIN 5234	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	

Technical details	
Clamping width	60 mm
Capacities for pipes (diameter)	Ø 2 3/8
Capacities for pipes (diameter)	Ø 60 mm
Capacities for nuts	60 mm
Inner diameter, inches	Ø 1 1/2 Inch

technical change and errors excepted

