

Product information

83 20 020

Pipe Wrench 45°

DIN 5234



₩ 45°

- · Swedish pattern
- 45° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General	
Article No.	83 20 020
EAN	4003773014232
Pliers	red powder-coated
Weight	2,596 g
Dimensions	570 x 72 x 28 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details		
Clamping width	70 mm	
Capacities for pipes (diameter)	Ø 2 3/4 Inch	
Capacities for pipes (diameter)	Ø 70 mm	
Capacities for nuts	70 mm	
Inner diameter, inches	Ø 2 Inch	

technical change and errors excepted

