

Product information

83 30 030

Pipe Wrench S-Type

DIN 5234



- · Slim, S-type jaw
- Jaws with offset teeth in opposite direction Teeth additionally induction-hardened
- Three-point contact on pipes, self-locking
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General	
Article No.	83 30 030
EAN	4003773014164
Pliers	red powder-coated
Weight	4,366 g
Dimensions	680 x 87 x 31 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Clamping width	100 mm
Capacities for pipes (diameter)	Ø 4 3/4
Capacities for pipes (diameter)	Ø 120 mm
Capacities for nuts	120 mm
Inner diameter, inches	Ø 3 Inch

technical change and errors excepted



