

Product information

83 61 015

Pipe Wrench S-Type

With fast adjustment



• Pinch guard prevents operators' fingers being pinched

- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Maximum load capability thanks to completely hardened handles
 Gripping jaws with specially hardened teeth, hardness approx. 56
- HRCChrome vanadium electric steel, forged, multi stage oil-hardened

General	
Article No.	83 61 015
EAN	4003773077619
Pliers	grey powder-coated
Handles	plastic coated
Weight	1,470 g
Dimensions	420 x 84 x 28 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	
Clamping width	60 mm
Capacities for pipes (diameter)	Ø 2 3/8 Inch
Capacities for pipes (diameter)	Ø 60 mm
Capacities for nuts	60 mm
Inner diameter, inches	Ø 1 1/2 Inch
Pipe inner dia.	37.5 mm
Dimensions REACH compliant RoHS compliant Technical details Clamping width Capacities for pipes (diameter) Capacities for pipes (diameter) Capacities for nuts Inner diameter, inches	420 x 84 x 28 mm contains SVHC not applicable 60 mm Ø 2 3/8 Inch Ø 60 mm 60 mm Ø 1 1/2 Inch

technical change and errors excepted





KNIPEX Quality – Made in Germany



