

Product information

87 00 100 BK

KNIPEX Cobra® XS

Pipe Wrench and Water Pump Pliers

DIN ISO 8976



- Optimum accessibility, even in confined spaces: particularly compact design, very slim head
- One-handed fine adjustment by pushing for the simplest adjustment to different workpiece sizes
- Long-lasting secure grip ensured by high wear resistance
- Gripping capacity Ø 28 mm, width across flats up to 24 mm – at only 100 mm length
- Box joint: high quality and durability provided by dual guide
- Gripping surfaces with specially hardened teeth, hardness approx. 60 HRC
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Pinch guard prevents operators' fingers being pinched
- Fine adjustment with 11 adjustment positions

General

Article No.	87 00 100 BK
EAN	4003773085843
Pliers	grey atramentized
Head	polished
Handles	embossed, rough surface
Weight	87 g
Dimensions	100 x 30 x 10 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Adjustment positions	11
Kapazität für Rohre (Zoll)	Ø 1 Inch
Capacities for nuts	24 mm
Capacities for pipes (diameter)	Ø 28 mm

technical change and errors excepted



Self-locking and durable – all part of genuine KNIPEX water pump pliers



