

## Product information

# 87 02 180

### KNIPEX Cobra®

#### High-Tech Water Pump Pliers

DIN ISO 8976

- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	87 02 180
EAN	4003773042396
Pliers	grey atramentized
Head	polished
Handles	with multi-component grips
Weight	196 g
Dimensions	180 x 55 x 18 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Adjustment positions	18
Kapazität für Rohre (Zoll)	Ø 1 1/2 Inch
Capacities for nuts	36 mm
Capacities for pipes (diameter)	Ø 42 mm

technical change and errors excepted



Teeth set against the direction of rotation have a self-locking effect and prevent slipping on the workpiece.



