

Product information

87 02 250

KNIPEX Cobra®

High-Tech Water Pump Pliers



- With slim multi-component grips without collar for better handling and easier transport
- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

General	
Article No.	87 02 250
EAN	4003773040316
Pliers	grey atramentized
Head	polished
Handles	with slim multi-component grips
Weight	366 g
Dimensions	250 x 50 x 18 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Adjustment positions	25
Kapazität für Rohre (Zoll)	Ø 2 Inch
Capacities for nuts	46 mm
Capacities for pipes (diameter)	Ø 50 mm

technical change and errors excepted





KNIPEX Quality – Made in Germany













