

Product information

87 03 125

KNIPEX Cobra®

High-Tech Water Pump Pliers

DIN ISO 8976



- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	87 03 125
EAN	4003773073949
Pliers	chrome-plated
Head	chrome-plated
Handles	with non-slip plastic coating
Weight	85 g
Dimensions	125 x 38 x 14 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Adjustment positions	13
Kapazität für Rohre (Zoll)	Ø 1 Inch
Capacities for nuts	27 mm
Capacities for pipes (diameter)	Ø 29 mm

technical change and errors excepted



