

Product information

88 02 300 T

KNIPEX Alligator®

Water Pump Pliers

DIN ISO 8976



- Pliers with tether attachment point for mounting a fall protection system
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Robust construction, insensitive to dirt; particularly suitable for outdoor
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	88 02 300 T
EAN	4003773080183
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	595 g
Dimensions	300 x 65 x 25 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Adjustment positions	9
Capacity for pipes, inches (diameter)	Ø 2 3/4 Inch
Capacities for nuts	60 mm
Capacities for pipes (diameter)	Ø 70 mm
Drop Protection System	yes

technical change and errors excepted

KNIPEX Quality – Made in Germany










Self-locking on pipes and nuts: no slipping on the workpiece; the complete actuating force can be used to turn the workpieces; not having to squeeze the pliers handles reduces the required effort







KNIPEX Quality – Made in Germany





