KNIPEX Quality – Made in Germany



Product information

88 03 250

KNIPEX Alligator®

Water Pump Pliers

DIN ISO 8976



- Good access to the workpiece due to slim size of head and joint area
- More output and comfort compared to conventional water pump pliers of the same length: 9-notch adjustment positioning for 30 % more gripping capacity
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Robust construction, insensitive to dirt; particularly suitable for outdoor work
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

You Tube

General

General	
Article No.	88 03 250
EAN	4003773005742
Pliers	chrome-plated
Head	chrome-plated
Handles	with non-slip plastic coating
Weight	319 g
Dimensions	250 x 50 x 13 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Adjustment positions	9
Capacity for pipes, inches (diameter)	Ø 2
Capacities for nuts	46 mm
Capacities for pipes (diameter)	Ø 50 mm

technical change and errors excepted











Self-locking on pipes and nuts: no slipping on the workpiece; the complete actuating force can be used to turn the workpieces; not having to squeeze the pilers handles reduces the required effort







