

Product information

90 20 185

KNIPEX PlastiCut®

Cutter for flexible hoses and plastic conduit pipes •

- For cutting thin walled plastic pipes (conduit plastic pipes) and flexible hoses, also with fabric reinforcement, of plastic and rubber up to Ø 25 mm / 1"
- Not suitable for cutting cables
- With opening spring and locking device
- Blades: special tool steel, oil-hardened, interchangeable
- Tool body: glass fibre reinforced plastic



WW

General	
Article No.	90 20 185
EAN	4003773067122
Head	chrome-plated
Handles	glass fibre reinforced plastic handles
Weight	172 g
Dimensions	185 x 70 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities (diameter)	Ø 25 mm
Cutting edge length mm	Ø 25 mm

technical change and errors excepted



With replaceable blade



KNIPEX Quality – Made in Germany



