

Product information

90 25 20

Pipe Cutter

For composite pipes and protective tubes

- For cutting composite pipes $\varnothing 12.0$ to 25.0 mm and for cutting flexible protective tubes $\varnothing 18.0$ - 35.0 mm without damaging a potential pipe inside
- A calibration arbor can be fitted, for example for Geberit composite pipes with $\varnothing 11.5$ and 15.0 mm
- Blades: special tool steel, oil-hardened, interchangeable
- Tool body: high-grade chrome vanadium electric steel, oil-hardened



MM

General

| | |
|-----------------|----------------------------|
| Article No. | 90 25 20 |
| EAN | 4003773046004 |
| Pliers | galvanized |
| Handles | with multi-component grips |
| Weight | 332 g |
| Dimensions | 210 x 70 x 20 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|--------------------------|
| Cutting capacities composite pipes (diameter) | $\varnothing 12 - 25$ mm |
| Blade length | 25 mm |
| Cutting capacities protective tubes (diameter) | $\varnothing 18 - 35$ mm |

technical change and errors excepted



Clean cut of protective tubes $\varnothing 18 - 35$ mm



Composite pipes of $\varnothing 12 - 25$ are cut cleanly and without deformation