

## **Product information**

## 90 42 340

## **Punch Lock Riveter**



- To join metal section sheets used in dry walling for dividing walls and drop ceilings, without needing screws or rivets
  For U- and C-shaped sections with max 1.2 mm metal (2 x 0.6 mm)
- Minimum handforce required due to optimum lever transmission
- Pliers body: special tool steel, rolled, oil-hardened

General	
Article No.	90 42 340
EAN	4003773071884
Pliers	burnished
Handles	with multi-component grips
Weight	901 g
Dimensions	340 x 96 x 19 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Capacity in millimetres	max. 1.2 (2 x 0.6)

technical change and errors excepted



