

**Product information** 

## 90 49 340 M

Spare die for 90 42 340

- To join metal section sheets used in dry walling for dividing walls and drop ceilings, without needing screws or rivets
- For U- and C-shaped sections with max 1.2 mm metal (2 x 0.6 mm)
- Minimum handforce required due to optimum lever transmission
- Pliers body: special tool steel, rolled, oil-hardened



## General

General	
Article No.	90 49 340 M
EAN	4003773028499
Weight	91 g
Dimensions	120 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted