

Product information

92 51 01


Precision Tweezers



- For particularly demanding precision work: tough and highly resistant to corrosion
- Handcrafted: polished edges and an excellent matt, scratch-free and non-reflective surface
- For the electronics industry, watchmakers, jewellers, laboratories with biological and medical applications in moderately aggressive chemical environments
- High-quality premium stainless steel: high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- Ideally suited for microscopic work, precision handling, repairs, manufacturing electronic components, as well as other general applications; tips are guaranteed to have perfect symmetry and balance
- Also available as a set (92 00 02)
- Premium stainless steel

General		
Article No.	92 51 01	
Reference number	2A.SA.0	
EAN	4003773085126	
Material	premium stainless steel	
Gripping surfaces	smooth gripping surfaces	
Weight	15 g	
Dimensions	120 x 10 x 11 mm	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	

Technical details		
Surface	matt finish	
Finish	straight	
Tips width (A)	0.13 mm	
Tips width (B)	1.9 mm	
Tweezers tip version	blunt	
Corrosion-resistant	yes	
ESD-tested	no	
VDE tested	no	
Sectors	Industry electronics	
Magnetic	non-magnetisable (80%)	



technical change and errors excepted