

Product information

92 61 02

Universal Tweezers





- Universal Tweezers are suitable for demanding standard applications and precision tasks
- Wide range of designs: straight, angled, gripping surfaces and handles smooth or serrated, with needle points, narrow or blunt tips, as well as different lengths
- For the electronics industry, watchmakers and jewellers
- High quality stainless steel: extremely tough and very good corrosion resistance against a variety of atmospheric environments and many corrosive materials
- Stainless steel

General

Article No.	92 61 02
Reference number	7330.SA.B
EAN	4003773085133
Material	stainless steel
Gripping surfaces	knurled gripping surfaces
Weight	114 g
Dimensions	300 x 15 x 22 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Surface	matt finish
Finish	straight
Tips width (A)	2.5 mm
Tips width (B)	4.7 mm
Tweezers tip version	blunt
Corrosion-resistant	yes
Acid resistance	very good
ESD-tested	no
VDE tested	no
Sectors	Industry
Magnetic	non-magnetisable (80%)



technical change and errors excepted