

Product information

94 55 200

Anvil shears



MM

- Drawing cut against firm surface for cutting soft materials without damage, e.g. rubber profiles, PVC, leather, wood, hoses etc.
 Cuts flat material with a max. width of 40 mm and height of 7.5 mm
- Cutting capacity for round material up to Ø 25 mm
- Strong, replaceable blade
- With opening spring and locking device
- Tool body: tool steel, rolled, oil-hardened

General	
Article No.	94 55 200
EAN	4003773080763
Shears	chrome-plated
Handles	with plastic grips
Weight	290 g
Dimensions	200 x 75 x 22 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details Blade length 40.0 mm

technical change and errors excepted





KNIPEX Quality – Made in Germany













