

Product information

95 05 165

Cable Shears

Handles extrusion plastic-coated



WW

- Cuts cables up to Ø 10 mm / 24 mm²
- With opening spring and locking device
- Blades made of stainless steel
- · Oil-hardened and tempered
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- No crushing, slight deformation of the cable only
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Shears body: surgical steel, stainless, vacuum-hardened
- Handles: plastic, impact-proof

Article No. 95 05 165 EAN 4003773019596	
EAN 4003773019596	
Head polished	
Handles plastic coated	
Weight 111 g	
Dimensions 165 x 48 x 16 mm	
REACH compliant does not contain SVH0	C
RoHS compliant not applicable	

Technical details	
Cutting capacity copper cable, multiple- stranded	24 mm²
Cutting capacity copper cable, multiple- stranded	Ø 10 mm
AWG	4

technical change and errors excepted