

Product information

95 06 230

Cable Shears

Handles extrusion plastic-coated

IEC 60900 DIN EN 60900



☆1000 V

- For copper single conductors up to 16 mm², multiple stranded wires up to 50 mm², fine stranded up to 70 mm² and aluminium conductors multiple stranded wires up to 70 mm²
- Easy cutting with one-hand operation due to high transmission ratio
- Stainless special grade steel, oil-hardened and tempered
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- No crushing, slight deformation of the cable only
- Adjustable bolted joint
- Shears body: surgical steel, stainless, vacuum-hardened
- Handles: plastic, impact-proof

General	
Article No.	95 06 230
EAN	4003773006305
Head	polished
Handles	plastic insulated, VDE-tested
Weight	274 g
Dimensions	230 x 82 x 30 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	50 mm ²
Cutting capacity copper cable, multiple- stranded	Ø 16 mm
AWG	1/0
VDE tested	yes

technical change and errors excepted