

Product information

95 12 165

Cable Shears



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Clean and smooth cut without crushing and deformation
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Easy cutting with one-hand operation
- With guard
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened

General	
Article No.	95 12 165
EAN	4003773029182
Shears	burnished
Handles	with multi-component grips
Weight	250 g
Dimensions	165 x 52 x 22 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	50 mm ²
Cutting capacity copper cable, multiple- stranded	Ø 15 mm
AWG	1 / 0

technical change and errors excepted



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable