

Product information

95 12 200

Cable Shears

With twin cutting edge



- For cutting copper and aluminium cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- By dividing the cutting actions into initial cut (insulating sheath in the front cutting area) and final cut (conductor in the back cutting area), cables up to Ø 20 mm can be cut in one-hand operation
- Low handforce required due to favourable lever ratio and special blade geometry
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened

General	
Article No.	95 12 200
EAN	4003773047834
Shears	burnished
Handles	with multi-component grips
Weight	324 g
Dimensions	200 x 55 x 21 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	70 mm ²
Cutting capacity copper cable, multiple- stranded	Ø 20 mm
AWG	2/0

technical change and errors excepted



Final cut: after cutting the sheath in the front profile the conductors in the rear part are cut. Initial cut in the front profile, final cut in the rear profile - to keep it as easy as possible.



Initial cut: using the front cutting edge to cut the insulating sheath on larger cable diameters leaves an ergonomic