

## **Product information**

## 95 21 600

## **Cable Shears**

For two-hand operation



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and wire ropes
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Favourable lever ratio due to toggle lever
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Bolted cutter head, replaceable
- Handles: steel tube
- Cutter head: high-grade chrome vanadium electric steel, forged, oilhardened

General	
Article No.	95 21 600
EAN	4003773025252
Head	polished
Handles	with plastic grips
Weight	1,862 g
Dimensions	600 x 165 x 38 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	150 mm <sup>2</sup>
Cutting capacity copper cable, multiple- stranded	Ø 27 mm
AWG	6 / 0

technical change and errors excepted