

Product information

95 39 870

Movable spare blade for 95 31 870 / 95 32 100 :



- For copper and aluminium single conductors as well as multiple stranded cables also with hard rubber or plastic sheath
- Not suitable for steel wire and wire ropes
- Also suitable for cables with iron sheath reinforcement
- Little hand force required for cutting due to optimum transmission ratio
- High cutting capacity due to two-hand operation and ratchet action
- The blade can be opened in any cutting position
- Handle length with multiple position adjustment from 400 610 mm (short transport length, individual adaptation to working conditions)
- Blade: special-quality high-grade tool steel, oil-hardened
- Handles: high-strength oval aluminium tubing

General	
Article No.	95 39 870
EAN	4003773025306
Weight	1,350 g
Dimensions	170 x 5 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted