

Product information

95 62 190 T

Wire Rope Cutter

Forged



- Pliers with tether attachment point for mounting a fall protection system
- With two crimping dies for end caps on Bowden cable sheaths and end ferrules for traction cables
- Comfortable work thanks to handy, slim design and internal opening spring
- Bolted joint for precise blade guidance, re-adjustable
- High leverage for reduced effort
- Cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

WW



General	
Article No.	95 62 190 T
EAN	4003773080206
Head	burnished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	345 g
Dimensions	190 x 66 x 24 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities piano wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple- stranded (diameter)	Ø 7.0 mm
Cutting capacities wire rope (diameter)	Ø 5.0 mm
Cutting capacities medium hard wire (diameter)	Ø 4.0 mm
AWG	8
Drop Protection System	yes

technical change and errors excepted


KNIPEX Quality – Made in Germany











Internal opening spring