

Product information

95 71 600

Wire Rope and ACSR-Cable Cutter



- For wire ropes and steel rods, copper and aluminium cables
- Suitable for cutting overhead cables with strain relief wire (ACSRcables)
- Angular cutting blades allow cutting of single rope wire
- Optimum transmission ratio for high cutting performance
- Bolted cutter head, replaceable
- Low weight
- Handles: aluminium, high-strength
- Cutter head: high-grade special tool steel, multi stage oil-hardened

General	
Article No.	95 71 600
EAN	4003773014539
Head	polished
Handles	with plastic grips
Weight	1,716 g
Dimensions	600 x 151 x 25 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple- stranded	150 mm²
Cutting capacity copper cable, fine-stranded (diameter)	Ø 14.0 mm
Cutting capacities wire rope (diameter)	Ø 14.0 mm
Cutting capacities medium hard wire (diameter)	Ø 9.0 mm
Cutting capacites iron (diameter)	Ø 9 mm
AWG	6 / 0

technical change and errors excepted

