

## Product information

# 95 81 600

## Wire Rope and ACSR-Cable Cutter



- With reinforced cutter head for higher performance, also cuts piano wire
- For wire ropes and steel rods, copper and aluminium cables
- Suitable for cutting overhead cables with strain relief wire (ACSR-cables)
- Angular cutting blades allow cutting of single rope wire
- Optimum transmission ratio for high cutting performance
- Bolted cutter head, replaceable
- Low weight
- Handles: aluminium, high-strength
- Cutter head: high-grade special tool steel, multi stage oil-hardened

### General

Article No.	95 81 600
EAN	4003773025344
Head	polished
Handles	with plastic grips
Weight	2,256 g
Dimensions	600 x 165 x 58 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacity copper cable, multiple-stranded	150 mm <sup>2</sup>
Cutting capacity copper cable, fine-stranded (diameter)	Ø 16.0 mm
Cutting capacities wire rope (diameter)	Ø 16.0 mm
Cutting capacities medium hard wire (diameter)	Ø 10.0 mm
Cutting capacities piano wire (diameter)	Ø 4.5 mm
Cutting capacities iron (diameter)	Ø 10 mm
AWG	6 / 0

*technical change and errors excepted*

