

Product information

97 21 215

Crimping Pliers




- For cutting cables, stripping wire and crimping insulated and non-
- insulated terminals, connectors and plug type connectors
 With threaded holes for cutting copper and brass screws threaded M $2.6\,/\,M$ 3 / M $3.5\,/\,M$ 4 and M 5
- Bolted joint for higher stability and even movement
- Special steel, high-strength

General	
Article No.	97 21 215
EAN	4003773019688
Pliers	black lacquered
Handles	with multi-component grips
Weight	250 g
Dimensions	230 x 63 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Application	insulated terminals + cable connectors
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

technical change and errors excepted



97 21 215

KNIPEX Quality – Made in Germany



