

Product information

97 39 05

Crimping die

For non-insulated open plug type connectors
(plug width 4.8 + 6.3 mm)

- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Special quality chrome vanadium electric steel, oil-hardened
- Round magazine: glass fibre reinforced plastic



General

Article No.	97 39 05
EAN	4003773070078
Weight	45 g
Dimensions	32 x 12 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

technical change and errors excepted