

Product information

97 39 09

Crimping die

For insulated and non-insulated wire ferrules



- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Special quality chrome vanadium electric steel, oil-hardened
- Round magazine: glass fibre reinforced plastic

General	
Article No.	97 39 09
EAN	4003773077763
Weight	50 g
Dimensions	50 x 12 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details		
Application	for wire ferrules	
Capacity in square millimetres	10.0 / 16.0 / 25.0 mm²	
AWG	8/6/4	

technical change and errors excepted