

## Product information

# 97 43 05

## Crimp System Pliers

For exchangeable crimping dies



- With attached crimping dies for non-insulated open plug-type connectors (4.8 and 6.3 mm connector width)
- Just one tool for almost 1000 crimping applications
- Almost parallel crimping motion
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Ergonomically designed handles
- Different locators for precise positioning of the connectors
- Crimping dies for applications not covered in the range offered here, may be available on request
- Special quality chrome vanadium electric steel, oil-hardened

### General

Article No.	97 43 05
EAN	4003773031031
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	618 g
Dimensions	200 x 96 x 17 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details



Application	Crimp System Pliers for non-insulated open plug-type connectors (4.8 and 6.3 mm connector width)
Capacity in square millimetres	0.5 — 6.0 mm <sup>2</sup>
Number of crimping positions	3
AWG	20 — 10

*technical change and errors excepted*