

## Product information

# 97 49 05

- Application: non-insulated open plug type connectors (plug width 4.8 + 6.3 mm) 0.5 - 6.0 mm<sup>2</sup>

### Crimping die

For non-insulated open plug-type connectors 4.8 + 6.3 mm



#### General

Article No.	97 49 05
EAN	4003773030867
Weight	46 g
Dimensions	50 x 10 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

#### Technical details



Application	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
Capacity in square millimetres	0.5 — 6 mm <sup>2</sup>
Number of crimping positions	3
AWG	20 — 10

*technical change and errors excepted*