

Product information

97 49 14

Crimping die

For non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267

 Application: for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and noninsulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267





General

General		
Article No.	97 49 14	
EAN	4003773077756	
Weight	37 g	
Dimensions	50 x 17 mm	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	
Technical details		

Application	for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
Capacity in square millimetres	0.5 — 10 mm²
Number of crimping positions	4
AWG	20 — 8

technical change and errors excepted