

Product information

97 49 19

- Application: insulated + non-insulated wire ferrules 35 - 50 mm²

Crimping die


For wire ferrules



General

Article No.	97 49 19
EAN	4003773030898
Weight	46 g
Dimensions	50 x 12 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	insulated and non-insulated wire ferrules
Capacity in square millimetres	35 — 50 mm ²
Number of crimping positions	2
AWG	2 / 0

technical change and errors excepted