

## **Product information**

## 97 51 12

## **Crimping Pliers for Western plugs**



- Improved opening mechanism, optimised design, less weight
- Can be used to crimp 4-, 6- and 8-pin Western plugs
- For cutting and stripping unshielded ribbon telephone cables
- Precise crimping process thanks to parallel crimping
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Optimum transmission of force due to lever action for fatigue-reduced operation
- For Western plug type RJ 10 (7.65 mm wide), RJ 11/12 (9.65 mm wide) and RJ 45 (11.68 mm wide) long design
- With length cutter and stripping knife for ribbon cables 6 and 12 mm length
- Head burnished, handles with two-colour multi-component grips
- With additional stripping device for round cables
- Special quality chrome vanadium electric steel, oil-hardened

General

MM 🔤 🥯 🐋

General	
Article No.	97 51 12
EAN	4003773043188
Pliers	burnished
Handles	with multi-component grips
Weight	475 g
Dimensions	200 x 63 x 18 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

## **Technical details**



Capacity	RJ 10 (4-poles) 7.65 mm RJ 11/12 (6-poles) 9.65 mm RJ 45 (8- poles) 11.68 mm
Number of crimping positions	3
Range of applications	Western plugs

technical change and errors excepted