KNIPEX Quality – Made in Germany



Product information

97 52 04

Crimping Pliers

For two-hand operation



- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Two-hand operation for easy crimping of large conductor diameters
 Easy handling as a result of well balanced centre of gravity, angled head and ergnomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General

Article No. 97 52 04 EAN 4003773025450 Pliers burnished Head burnished Handles with non-slip plastic grips Weight 562 g Dimensions 250 x 82 x 27 mm **REACH** compliant contains SVHC **RoHS** compliant not applicable


Technical details



Application	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 2.5 mm ²
Number of crimping positions	4
AWG	26 — 14

technical change and errors excepted





KNIPEX Quality – Made in Germany



Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm², twohand operation is possible by the longer handles



First step: move the handle with two fingers only until both jaws touch the connector to be crimped