KNIPEX Quality – Made in Germany



Product information

97 52 08

Crimping Pliers

For two-hand operation



- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Two-hand operation for easy crimping of large conductor diameters
 Easy handling as a result of well balanced centre of gravity, angled head and ergnomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General	
Article No.	97 52 08
EAN	4003773025481
Pliers	burnished
Head	burnished
Handles	with non-slip plastic grips
Weight	565 g
Dimensions	250 x 75 x 23 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



Application	insulated and non-insulated wire ferrules
Capacity in square millimetres	0.25 — 6 mm ²
Number of crimping positions	5
AWG	24 — 10

technical change and errors excepted

KNIPEX Quality – Made in Germany







Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm², twohand operation is possible by the longer handles



First step: move the handle with two fingers only until both jaws touch the connector to be crimped