KNIPEX Quality – Made in Germany



Product information

97 52 18

Crimping Pliers

For two-hand operation



The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers Consistently bick estimates quality thanks to precision disc and retain

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Two-hand operation for easy crimping of large conductor diameters
 Easy handling as a result of well balanced centre of gravity, angled
- head and ergnomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



Article No.	97 52 18
EAN	4003773026839
Pliers	burnished
Head	burnished
Handles	with non-slip plastic coating
Weight	571 g
Dimensions	250 x 78 x 26 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	

Technical details



Application	Twin wire ferrules 2x6 / 2x10 / 2x16 mm ²
Capacity in square millimetres	16 mm ²
Number of crimping positions	3
AWG	10
AWG	2 x 10 / 2 x 8 / 2 x 6

technical change and errors excepted

KNIPEX Quality – Made in Germany















KNIPEX Quality – Made in Germany







