

## Product information

# 97 52 63

## Four-Mandrel Crimping Pliers for turned contacts



- Fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- Pliers in a plastic case with foam insert and standard locator for precise positioning of the contacts
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Special quality chrome vanadium electric steel, oil-hardened



### General

Article No.	97 52 63
EAN	4003773050148
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	388 g
Dimensions	180 x 67 x 37 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details



Application	turned contacts
Capacity in square millimetres	0.08 — 2.5 mm <sup>2</sup>
AWG	28 — 14
Number of crimping positions	1
Max. contact diameter	5 mm

technical change and errors excepted



Standard locator



multi-functional digital display, adjustment in mm, inch or comparable selection positions according to MIL