

## Product information

# 97 53 04

## Self-Adjusting Crimping Pliers for wire ferrules

With lateral access




- Narrow handle width and improved ergonomics
- Square compression now for wire ferrules up to 16 mm<sup>2</sup>
- Square compression for ideal contact surfaces in the clamp connection
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm<sup>2</sup> or 2 x AWG 12
- Reliable hexagonal crimping of wire ferrules from 0.08 to 16 mm<sup>2</sup> (AWG 6) by simply turning and setting the adjusting wheel and all twin wire ferrules up to 2 x 10 mm<sup>2</sup> (AWG 2 x 8)
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Special quality chrome vanadium electric steel, oil-hardened



### General

Article No.	97 53 04
EAN	4003773028017
Pliers	burnished
Handles	with multi-component grips
Weight	459 g
Dimensions	180 x 77 x 21 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details



Application	Wire ferrules
Capacity in square millimetres	0.08 — 10 / 16 mm <sup>2</sup>
Number of crimping positions	1
AWG	28 — 6

technical change and errors excepted



Crimping capacity can be switched over simply from 10 mm<sup>2</sup> to 16 mm<sup>2</sup>.

